



# HF-Matchbox Blue

## HF-M BLUE 124 LH TL/TL5/PL-L 230-240V

HF-Matchbox Blue is an affordable, reliable, compact, lightweight and high-frequency ballast for use with system wattages below 25 W in combination with TL mini, TL-D, TL5 and TL5c, PL-T/C, and PL-L/S lamps. The HF-M Blue range has a robust design, meets all relevant international safety and performance standards and has an energy efficiency index (CELMA EEI ) of A2.


### Product data

Operating and Electrical	
Input Voltage	230 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Number of Products on MCB (16A Type B) (Nom)	60
Wiring	
Connector Type Input Terminals	Insert
Color Input Terminals	Orange
Color Output Terminals	Grey
Connector Type Output Terminals	Insert
Cable Length From Device to Lamp	59-1/16 inch
Temperature	
Ambient temperature range	14 °F to 104 °F
T-Case Maximum (Max)	167 °F
Mechanical and Housing	
Housing	LH

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Approval Marks	F-Marking CE marking VDE certificate CB Certificate
Product Data	
Order product name	HF-M BLUE 124 LH TL/TL5/PL-L 230-240V
Full product name	HF-M BLUE 124 LH TL/TL5/PL-L 230-240V
Full product code	871150053640230
Order code	913700418066
Material Nr. (12NC)	913700418066
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500536402
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500536419

HF-Matchbox Blue

Dimensional drawing



Product	A1	A2	B1	C1	D1
HF-M BLUE 124 LH TL/TL5/PL-L 230-240V	7-3/8 inch	7-1/8 inch	7/8 inch	7/8 inch	3/16 inch

Product
HF-M BLUE 124 LH TL/TL5/PL-L 230-240V

