



HF-Matchbox Red

HF-M RED 118 SH PL-C/PL-T 230-240V

HF-Matchbox Red is an affordable, reliable, compact, lightweight and high-frequency ballast for use with system wattages below 25 W in combination with TL mini, TL-D, TL5 and TL5c, PL-T/C, and PL-L/S lamps. The HF-M Red range has a robust design, meets all relevant international safety and performance standards and has an energy efficiency index (CELMA EEI) of A2.

Product data

General Information	
Lamp type	PL-C/PL-T
Number of lamps	1 piece/unit
Number of products on MCB (16 A type B) (nom.)	73
Automatic restart	Yes
Operating and Electrical	
Input Voltage	230 to 240 V
Input frequency	50 to 60 Hz
Power factor 100% load (nom.)	0.62
Ignition time (max.)	0.45 s
Mains voltage performance (AC)	-8%+6%
Mains voltage safety (AC)	-10%+10%
Power losses (nom.)	2.0-2.1 W
Wiring	
Connector type input terminals	Insert
Colour input terminals	Orange
Colour output terminals	Grey
Connector type output terminals	Insert
Cable length from device to lamp	1.50 m

Cable length hot-wiring	0.30 m
Wire strip length	8.0-9.0 mm
Input terminal cross section	0.50-1.50 mm ²
Output terminal cross section	0.50-1.50 mm ²

System characteristics

Rated ballast-lamp power	18 W
Rated lamp power on PL-T	18 W
System power on PL-T	17.3 W
Power loss on PL-T	2.1 W
Lamp power on PL-T	15.2 W
System power on PL-C	17.9 W
Rated lamp power on PL-C	18 W
Power loss on PL-C	2 W
Lamp power on PL-C	15.9 W

Temperature

T-ambient (max.)	40 °C
T-ambient (min.)	-10 °C
T-Case maximum (max.)	75 °C

HF-Matchbox Red

Mechanical and Housing

Housing SH

Emergency Operation

Battery voltage lamp ignition 194-254 V

Approval and Application

IP classification IP 20 [Ingress Protection 20]

Approval marks F-Marking CE marking ENEC certificate
CB Certificate

Product Data

Full product code 871150092802330

Order product name HF-M RED 118 SH PL-C/PL-T 230-240V

EAN/UPC – product 8711500928023

Order code 92802330

SAP numerator – quantity per pack 1

SAP numerator – packs per outer box 50

SAP material 913700423466

Net Weight (Piece) 0.034 kg

Dimensional drawing

A2

Product	D1	C1	C2	A1	A2	B1
HF-M RED 118 SH PL-C/PL-T 230-240V	4.4 mm	22.0 mm	10.0 mm	80.0 mm	70.0 mm	40.0 mm

HF-M RED 118 SH PL-C/PL-T 230-240V

