



# Standard

## STANDARD MAG BALLAST (1) 9W COMPACT(2-PIN) 120V

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.

### Product data

General Information	
Lamp Type	CFQ9W/G23
Number of Lamps	1 piece/unit
Lamp Footage	-
Ballast Type	Magnetic Fluorescent
Base Model	H1B9TPW
Suitable For Outdoor Use	Yes
Automatic Restart	Yes
Operating and Electrical	
Input Voltage	120 V
Input Frequency	60 Hz
Max THD	20 %
Starting Method	Preheat
Lamp Current Crest Factor (Nom)	1.5
Ignition Time (Nom)	1 s
Inp. Current (Open Circuit)	0.13
Input Current (Starting)	0.2
Ballast Factor (Nom)	0.92
Power Factor (Nom)	0.91
Input Current (Operating) (Nom)	0.1 A
Input Power (Nom)	11 W


Rated Lamp Watts	9 W
Wiring	
Wire Striplength	0.50/0.375 mm
Lamp Connection	Series
Wire Length by Color	See data sheet
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	No
Through Wiring Configuration Allowed	No
Max Ballast-Lamp Distance Remote Wiring	30'
Max Ballast-Lamp Distance Tandem Wiring	-
Max Ballast-Lamp Distance Through Wiring	-
Mechanical and Housing	
Housing Material	Metal
Housing	R1
Housing Dimensions	4.25" x 2.0" x 1.44"
Approval and Application	
EMC Immunity Standard	FCC Non-Consumer

## Standard

Approbation Marks	CSA certificate UL certificate RoHS Compliant
Sound Rating	A
UL Recognized	No
<b>Product Data</b>	
Order product name	STANDARD MAG BALLAST (1) 9W COMPACT(2-PIN) 120V

EAN/UPC - Product	781087068281
Order code	H1B9TPWM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	36
Material Nr. (12NC)	913700506409
Net Weight (Piece)	314.000 g

## Dimensional drawing



Product	A1	A2	B1	C1
STANDARD MAG BALLAST (1) 9W COMPACT(2-PIN) 120V	4.25 in	3.56 in	2 in	1.44 in

MAG BALLAST (1) 9W COMPACT(2-PIN) 120V

