




SmartMate

SMARTMATE ELE BALLAST (2) 18W CFL (4-PIN) 120-277V

Offering maximum versatility, the Philips Advance family of SmartMate ballasts for 4-pin compact fluorescent lamps drive a broad range of quad and triple-tube, circline, 2D, and long twin-tube lamps. SmartMate ballasts' energy efficient design, compact and lightweight housing, and user-friendly features make these ballasts an ideal choice for fixture manufacturers, retrofitters, and MRO replacement.

产品数据


基本信息	
灯具数量	1/2 件/单位
镇流器类型	Electronic Fluorescent
适用于户外	Yes
自动重新启动	Yes
运营和电气	
输入电压	120-277 V
输入频率	50 至 60 岁 Hz
美国总谐波变形	10 %
点火方法	程式化启动
峰值因数 (标称)	1.7
点火时间 (标称)	1.5 s
镇流器因数 (标称)	1
功率系数 (标称)	0.98
输入电流 (最大)	0.14 A
输入电流 (最小)	0.07 A
输入功率 (标称)	35-35 W
额定照明功率	18 W

接线方式	
颜色输入端	BLK & WHT
颜色输出端	RED, YEL & BLU
电线裸线长度	0.375 mm
灯具连接	Series
按颜色区分的电线长度	No wires
电线规格 (标称)	18AWG mm
电线类型	Solid
允许的远程布线配置	Yes
允许的串联布线配置	Yes
允许的通过式布线配置	Yes
最大镇流器到灯具距离远程布线	1-L = 15' / 2-L = 6'
最大镇流器到灯具距离串联布线	2-L: Red = 6'
最大镇流器到灯具距离通过式布线	2-L: Red = 6'
连接器类型	Poke-In
温度	
最大外壳温度 (标称)	75 °C
机械和壳体	
外壳材料	金属

外壳	H1
外壳尺寸	4.98" x 2.4" x 1.0"
应用	
Emc 抗干扰标准	FCC Non-Consumer
批准标志	CSA 认证证书 UL certificate RoHS compliance
湿度和噪声级别	A
产品参数	
订单产品名称	SMARTMATE ELE BALLAST (2) 18W CFL (4-PIN) 120-277V

EAN/UPC - 产品	781087102909
订购代码	913700508951
计算器 - 每个包中的数量	1
计算器 - 每个外包装箱中的包数	20
材料编号(12NC)	913700508951
净重 (每件)	0.168 kg

二维绘图



SMARTMATE ICF2S18H1LD35M

Product
SMARTMATE ELE BALLAST (2) 18W CFL (4-PIN) 120-277V

