



Standard

STANDARD MAG BALLAST (1) F8T5 PH 120V

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.

Product data

General Information					
Lamp Type	F8T5				
Number of Lamps	1 piece/unit				
Lamp Footage	-				
Ballast Type	Magnetic Fluorescent				
Base Model	LPL59				
Suitable For Outdoor Use	Yes				
Automatic Restart	Yes				
Operating and Electrical					
Input Voltage	120 V				
Input Frequency	60 Hz				
Max THD	10 %				
Starting Method	Preheat				
Lamp Current Crest Factor (Nom)	1.5				
Ignition Time (Nom)	1s				
Inp. Current (Open Circuit)	0				
Input Current (Starting)	0.19				
Ballast Factor (Nom)	1	_			
Power Factor (Nom)	0.53				
Input Current (Operating) (Nom)	0.14 A				
Input Power (Nom)	9 W				
Rated Lamp Watts	8 W	_			
		_			

Wiring					
Wire Striplength	0.50/0.375 mm				
Lamp Connection	Series				
Wire Length by Color	See data sheet				
Wire Gauge (Nom)	18AWG mm				
Wire Type	Solid				
Remote Wiring Configuration Allowed	Yes				
Tandem Wiring Configuration Allowed	No				
Through Wiring Configuration Allowed	No				
Max Ballast-Lamp Distance Remote Wiring	30'				
Max Ballast-Lamp Distance Tandem Wiring -					
Max Ballast-Lamp Distance Through Wiring -					
Mechanical and Housing					
Housing Material	Metal				
Housing	X1				
Housing Dimensions	2.38" x 1.38" x 1.38"				
Approval and Application					
EMC Immunity Standard	FCC Non-Consumer				
Approbation Marks	CSA certificate UL certificate RoHS				
	Compliant				
Sound Rating	A				


Datasheet, 2019, March 22 data subject to change

Standard

UL Recognized	No				
Product Data					
Order product name	STANDARD MAG BALLAST (1) F8T5 PH				
	120V				
EAN/UPC - Product	781087113905				
Order code	LPL59M				

umerator - Quantity Per Pack	1
umerator - Packs per outer box	135
laterial Nr. (12NC)	913700509609
et Weight (Piece)	0.123 kg
. ,	3.57003000

Dimensional drawing



MAG BALLAST (1) F8T5 PH 120V

Product	A1	A2	B1	C1	D1
STANDARD MAG BALLAST (1) F8T5 PH 120V	2.38 in	2 in	1.59 in	1.38 in	0.19 in



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.