



Lighting




Core & Coil (71A) MH 175W - 450W

Max Ballast-Lamp Distance Remote	Determined by AWG used
Wiring	
Recommended Fuse Value	10/5/4 A
Approval and Application	
Open Circuit Voltage Test (Volts)	270-330 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	D/D/D
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029D

Product Data	
Order product name	CORE & COIL HID MH BAL 400W M59 120/277/347V KIT
EAN/UPC - Product	781087096659
Order code	191890
Local order code	191890
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700525509
Net Weight (Piece)	5.884 kg

Dimensional drawing



MH BAL 400W M59 120/277/347V KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 400W M59 120/277/347V KIT	4 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in

