



Core & Coil (71A) MH 175W - 450W

CORE & COIL HID MH BAL 400W M135/155 QUAD KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information				
ANSI Code	M135-M155			
Lamp Type	400W MH			
Number of Lamps	1 piece/unit			
Circuit Type	SUPER-CWA			
Ballast Type	Magnetic HID			
Base Model	71A6092AEE			
Core Size	4 1/4 x 4 3/4 (2 coil)			
Suitable For Outdoor Use	Yes			
Ignitor Catalog Number	LI533-H4			
Ignitor Temperature Rating	105°C			
Capacitor Value	26 MFD			
Capacitor Catalog Number	7C260P33R			
Capacitor Requirements	330V			
Capacitor Temperature Rating	105°C			
Capacitor Diameter/Oval Dimensions	1.75 in			
Capacitor Height	4.8 in			
Automatic Restart	No			

Operating and Electrical						
Input Voltage	120/208/240/277 V					
Input Frequency	60 Hz					
Inp. Current (Open Circuit)	2.6/1.56/1.31/1.17 A					
Input Current (Starting)	2.97/1.68/1.48/1.3 A					
Input Current (Short Circuit)	2.4-3.6/1.4-2.1/1.2-1.8/1.05-1.55 A					
Secondary Short Circuit Current	3.6-4.5 A					
Constant Wattage Deviation	10%					
Ballast Factor (Nom)	1					
Power Factor (Nom)	0.90					
Nominal Open Circuit Voltage	275 V					
Input Current (Operating) (Nom)	3.8/2.2/1.9/1.65 A A					
Input Power (Nom)	452 W					
Rated Lamp Watts	400 W					
Wiring						
Wire Striplength	0.5 mm					
Wire Length by Color	12"					
Wire Type	Stranded					
Remote Wiring Configuration Allowed	Yes					


Datasheet, 2019, March 22 data subject to change

Core & Coil (71A) MH 175W - 450W

Max Ballast-Lamp Distance Remote	2'
Wiring	
Recommended Fuse Value	10/7/5/5 A
Approval and Application	
Open Circuit Voltage Test (Volts)	248-302 V
Approbation Marks	ULR CSA certificate EISA RoHS Compliant
Temperature Marking	D/D/D/D
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029D

Product Data			
Order product name	CORE & COIL HID MH BAL 400W M135/155		
	QUAD KIT		
EAN/UPC - Product	781087098035		
Order code	71A6092001D		
Numerator - Quantity Per Pack	1		
Numerator - Packs per outer box	1		
Material Nr. (12NC)	913700535809		
Net Weight (Piece)	5.983 kg		

Dimensional drawing



MH BAL 400W M135/155 QUAD KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 400W	4.1 in	2.16 in	4.8 in	4.4 in	4.3 in	3.9 in
M135/155 QUAD KIT						

