

Core & Coil (71A) HPS ~LT~ 200W

CORE & COIL HID HPS BAL 70W S62 120/208/240V C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	S62
Lamp Type	70W HPS
Number of Lamps	1 piece/unit
Circuit Type	CWI
Ballast Type	Magnetic HID
Base Model	71A79E6
Core Size	3 X 4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI551-J4
Ignitor Temperature Rating	105°C
Capacitor Value	24 MFD
Capacitor Catalog Number	7C240P30RA
Capacitor Requirements	300V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.65 in
Capacitor Height	3.7 in
Automatic Restart	No

Operating and Electrical	
Input Voltage	120/208/240 V
Input Frequency	60 Hz
Inp. Current (Open Circuit)	0.5/0.3/0.25 A
Input Current (Starting)	0.5/0.3/0.25 A
Input Current (Short Circuit)	0.25-0.4/0.15-0.25/0.12-0.2 A
Secondary Short Circuit Current	1.9-2.35 A
Constant Wattage Deviation	Within Trapezoid
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Nominal Open Circuit Voltage	110 V
Input Current (Operating) (Nom)	0.86/0.5/0.43 A A
Input Power (Nom)	95 W
Rated Lamp Watts	70 W

Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes


Core & Coil (71A) HPS ~LT~ 200W

Max Ballast-Lamp Distance Remote	2'
Wiring	
Recommended Fuse Value	3/2/2 A
Approval and Application	
Open Circuit Voltage Test (Volts)	100-120 V
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C/C/B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029C

Product Data

Order product name	CORE & COIL HID HPS BAL 70W S62 120/208/240V C&C
EAN/UPC - Product	781087050149
Order code	71A79E6500D
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	913700538009
Net Weight (Piece)	2.527 kg

Dimensional drawing



HPS BAL 70W S62 120/208/240V C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A79E6500D	2.9 in	1.6 in	3.9 in	3.5 in	2.8 in	2.4 in

