



Postline (74P)

POSTLINE HID HPS BAL 150W S55 120V POSTLINE

Lantern-type, post-top fixtures mounted on slender poles often require ballasts which fit in the poles. Postline ballasts include a special, elongated core and coil ballast encased and potted in a high temperature resin (Class H, 180°C max.) in cylindrical housings of a diameter to accommodate being placed within a 3" or 4" diameter pole.

Product data

General Information			
ANSI Code	S55	Power Factor (Nom)	0.91
Lamp Type	HPS	Nominal Open Circuit Voltage	120 V
Number of Lamps	1 piece/unit	Input Current (Operating) (Nom)	1.7 A A
Circuit Type	R-HPF	Input Power (Nom)	178 W
Ballast Type	Magnetic HID	Rated Lamp Watts	150 W
Base Model	74P8104	Wiring	
Suitable For Outdoor Use	Yes	Wire Striplength	0.50 mm
Ignitor Catalog Number	Inside Can	Wire Length by Color	12"
Capacitor Catalog Number	Inside Can	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Max Ballast-Lamp Distance Remote Wiring	5'
Input Voltage	120 V	Recommended Fuse Value	9 A
Input Frequency	60 Hz	Mechanical and Housing	
Inp. Current (Open Circuit)	2.5 A	Housing Material	Metal
Input Current (Starting)	3.6 A	Housing	74P
Input Current (Short Circuit)	2.9-4.3 A	Housing Dimensions	17.6" x 2.55" x 2.55"
Secondary Short Circuit Current	4.70-7.00 A	Approval and Application	
Constant Wattage Deviation	Within Trapezoid	Open Circuit Voltage Test (Volts)	108-132 V
Ballast Factor (Nom)	1		

Postline (74P)


Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029A

Product Data

Order product name	POSTLINE HID HPS BAL 150W S55 120V POSTLINE
--------------------	--

EAN/UPC - Product	781087481042
Order code	74P8104011P
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700547409
Net Weight (Piece)	3.815 kg

Dimensional drawing



HPS BAL 150W S55 120V POSTLINE

Product	B3	C1
POSTLINE HID 74P8104011P	2.55 in	17.6 in

