




Core & Coil (71A) HPS 200W - 400W

CORE & COIL HID HPS BAL 310W S67 QUAD KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data


General Information			
ANSI Code	S67	Input Frequency	60 Hz
Lamp Type	310W HPS	Input Current (Open Circuit)	1.8/1/0.9/0.8 A
Number of Lamps	1 piece/unit	Input Current (Starting)	1.7/0.89/0.85/0.75 A
Circuit Type	CWA	Input Current (Short Circuit)	1.4-2.2/0.8-1.25/0.7-1.1/0.6-0.95 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	4.4-5.4 A
Base Model	71A8371	Constant Wattage Deviation	Within Trapezoid
Core Size	4 x 4 (2 coil)	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	LI501-H4	Open Circuit Voltage	175 V
Ignitor Temperature Rating	105°C	Input Current (Nom)	3.37/1.94/1.68/1.45 A A
Capacitor Value	45 MFD	Input Power (Nom)	365 W
Capacitor Catalog Number	7C450P30RA	Rated Lamp Power	310 W
Capacitor Requirements	280V	Wiring	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.85 in	Wire Length by Color	12"
Capacitor Height	4.70 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Max Ballast-Lamp Distance Remote	2'
Input Voltage	120/208/240/277 V	Wiring	

Core & Coil (71A) HPS 200W - 400W

Recommended Fuse Value	8/5/5/5 A
Approval and Application	
Open Circuit Voltage Test (Volts)	155-195 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	D/C/D/B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029D

Product Data	
Order product name	CORE & COIL HID HPS BAL 310W S67 QUAD KIT
EAN/UPC - Product	781087837115
Order code	913700577609
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700577609
Net Weight (Piece)	6.519 kg

Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A8371001D	4.10 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in

HPS BAL 310W S67 QUAD KIT

