

Transformers

AUTO-TRANSFORMER AUTOXFMR 347:120/277 395VA C&C

Stepdown transformers and autotransformers are used when you need to connect a lower voltage device to a higher voltage source.


Product data

General Information	
Circuit Type	Transformer
Ballast Type	Magnetic HID
Base Model	71A9862
Core Size	7/8" E/I
Suitable For Outdoor Use	Yes
Operating and Electrical	
Input Voltage	347:(120/277) V
Input Frequency	60 Hz
Input Current (Nom)	0.92 A
Rated Lamp Power	395 VA load W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Mechanical and Housing	
Housing	NA

Housing Dimensions	NA
Approval and Application	
Approval Marks	CSA certificate RoHS Compliant
Temperature Marking	NA
UL Recognized	No
UL Insulation Class	H(180°C)
UL Temperature Code	NA
Product Data	
Order product name	AUTO-TRANSFORMER AUTOXFMR 347:120/277 395VA C&C
EAN/UPC - Product	781087046869
Order code	509604
Local order code	509604
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8
Material Nr. (12NC)	913700579009
Net Weight (Piece)	1.910 kg

Transformers

Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
AUTO-TRANSFORMER 71A9862600	3.9 in	2.7 in	2.6 in	2.2 in	2.2 in	1.8 in

AUTO-TRANSFORMER 71A9862600

