



# Outdoor Weatherproof (79W)

## OUTDOOR WEATHERPROOF HID MH BAL 175W M57 QUAD WP

Outdoor weatherproof ballasts are designed for remote mounting outdoors under all weather conditions. They may also be placed inside a pole base, but care must be taken to avoid areas prone to flood situations as they are not water submersable.

### Product data

General Information	
ANSI Code	M57ORM107
Lamp Type	MH
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	79W5590
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	Inside Can
Capacitor Catalog Number	Inside Can
Automatic Restart	No
Operating and Electrical	
Input Voltage	120/208/240/277 V
Input Frequency	60 Hz
Inp. Current (Open Circuit)	1.8/1.04/0.9/0.8 A
Input Current (Starting)	1.3/0.75/0.65/0.55 A
Input Current (Short Circuit)	0.85-1.25/0.45-0.7/0.4-0.6/0.3-0.5 A
Secondary Short Circuit Current	1.5-1.9 A
Constant Wattage Deviation	10%


Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Nominal Open Circuit Voltage	305 V
Input Current (Operating) (Nom)	1.8/1.04/0.9/0.8 A A
Input Power (Nom)	210 W
Rated Lamp Watts	175 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	10"
Wire Type	Stranded
Remote Wiring Configuration	Yes
Allowed	
Max Ballast-Lamp Distance Remote	Determined by AWG used
Wiring	
Recommended Fuse Value	5 A
Mechanical and Housing	
Housing Material	Metal
Housing	OW

## Outdoor Weatherproof (79W)

Housing Dimensions	6.6" x 6.38" x 6.38"
<b>Approval and Application</b>	
Open Circuit Voltage Test (Volts)	275-335 V
Approbation Marks	CSA certificate UL certificate RoHS Compliant
Temperature Marking	Max. case temperature 90°C
UL Recognized	No
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	NA

<b>Product Data</b>	
Order product name	OUTDOOR WEATHERPROOF HID MH BAL 175W M57 QUAD WP
EAN/UPC - Product	781087955901
Order code	79W5590001
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700583609
Net Weight (Piece)	5.176 kg

### Dimensional drawing



MH BAL 175W M57 QUAD WP

Product	B1	B2	B3	C1	C2
OUTDOOR WEATHERPROOF HID 79W5590001	7.3 in	6.4 in	1 in	6.6 in	1.9 in

