



PrimaVision Mini for CDM

HID-PV m PGJ5 20 /I CDM LPF 220-240V


Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

Product data

Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing	/I
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		
Earth Leakage Current (Max)	0.25 mA		
Inrush Current Width	0.40 ms		
Inrush Current Peak (Max)	30 A		
Number of Products on MCB (16A Type B) (Nom)	48		
Wiring		Approval and Application	
Cable Length From Device to Lamp	2 m	Approval Marks	F-Marking CE marking CB Certificate
Connector Type	Insert		
Temperature		Product Data	
Ambient temperature range	-20 °C to 50 °C	Order product name	HID-PV m PGJ5 20 /I CDM LPF 220-240V
T-Case Lifetime (Nom)	65 °C	Full product name	HID-PV m PGJ5 20 /I CDM LPF 220-240V
T-Case Maximum (Max)	75 °C	Full product code	871150090981730
		Order code	913700601666
		Material Nr. (12NC)	913700601666
		Local order code	HIDPVM20IMCDML
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500909817
		Numerator - Packs per outer box	12
		EAN/UPC - Case	8711500909824

PrimaVision Mini for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV m PGJ5 20 /I CDM LPF 220-240V	4.2 mm	30.0 mm	190.0 mm	154.0 mm	43.3 mm

