



# e-Vision Low Wattage 20-150W

## E-VISION ELE MH BAL 39W M130 / C179 120V

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

### Product data


General Information		Rated Lamp Watts	
ANSI Code	C130-M130,C179	39 W	
Lamp Type	39W MH		
Number of Lamps	1 piece/unit		
Ballast Type	Electronic HID		
Base Model	RMH39KLF		
Suitable For Outdoor Use	Yes		
Operating and Electrical		Wiring	
Input Voltage	120 V	Color Input Terminals	No terminals
Input Frequency	50 to 60 Hz	Color Output Terminals	No terminals
Max THD	15 %	Wire Striplength	0.50 mm
Lamp Current Crest Factor (Nom)	1.8	Control Wire Gauge	NA
Ignition Time (Nom)	1200 s	Wire Length by Color	All leads = 6"
Ballast Factor (Nom)	1	Wire Gauge (Nom)	18AWG mm
Power Factor (Nom)	0.90	Wire Type	Stranded
Input Current (Operating) (Max)	0.4 A	Remote Wiring Configuration Allowed	Yes
Input Current (Operating) (Min)	0.4 A	Tandem Wiring Configuration Allowed	No
Input Power (Nom)	45 W	Through Wiring Configuration Allowed	No
		Connector Type	No connector
		Temperature	
		T-Case Maximum (Nom)	90 °C
		Mechanical and Housing	
		Housing Material	Metal

e-Vision Low Wattage 20-150W

Housing	K
Housing Dimensions	4.1" x 1.3" x 1.2"
Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approbation Marks	CSA certificate UL certificate RoHS Compliant
Sound Rating	A
UL Recognized	No
Product Data	
Order product name	E-VISION ELE MH BAL 39W M130 / C179 120V

EAN/UPC - Product	781087051238
Order code	RMH39KLFM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913700612088
Net Weight (Piece)	178.000 g

Dimensional drawing



Product	A1	A2	A3	B1	B2	C1
E-VISION ELE MH BAL 39W M130 / C179 120V	4.4 in	4.1 in	4.5 in	1.1 in	0.5 in	1.2 in

E-VISION RMH39KLFM

