



# HF-Regulator II for TL5 lamps

## HF-R 2 14-35 TL5 EII 220-240V 50/60Hz

High-frequency electronic dimming ballast, using the analog protocol (1-10 V) for TL5 HE/HO and TL5 Eco lamps. The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.

### Product data


<b>Operating and Electrical</b>		<b>Temperature</b>	
Input Voltage	220 to 240 V	Ambient temperature range	-20 °C to 50 °C
Line Frequency	50 to 60 Hz	<b>Controls and Dimming</b>	
Input Frequency	50 to 60 Hz	Control Interface	1-10V
Earth Leakage Current (Max)	0.5 mA	<b>Mechanical and Housing</b>	
Inrush Current Width	0.40 ms	Housing	L 360x30x21
Inrush Current Peak (Max)	45 A	<b>Approval and Application</b>	
Number of Products on MCB (16A Type B) (Nom)	12	Ingress protection code	IP20 [Finger-protected]
<b>Wiring</b>		Energy Efficiency Index	A1 BAT
Connector Type Input Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]	Safety Standard	IEC 61347-2-3
Connector Type Output Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]	Environmental Standard	ISO 14001
		Approval Marks	CE marking ENEC certificate VDE-EMV certificate
		<b>Product Data</b>	
		Order product name	HF-R 2 14-35 TL5 EII 220-240V 50/60Hz

## HF-Regulator II for TL5 lamps

Full product name	HF-R 2 14-35 TL5 EII 220-240V 50/60Hz
Full product code	871150091178030
Order code	913700619566
Material Nr. (12NC)	913700619566
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8711500911780
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500911797

### Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-R 2 14-35 TL5 EII 220-240V 50/60Hz	4.2 mm	22 mm	360 mm	350 mm	30 mm

