



HF-Performer Intelligent for TL5 HE/HO lamps

HF-Pi 2 14/21/24/39 TL5 220-240V

HF-Performer Intelligent is a slim and lightweight high-frequency electronic ballast which makes it possible to exchange TL5 HE and HO lamps of the same length in order to maximize logistical flexibility in luminaire design and handling. With its smart power functionality based on Philips EII technology, HF-Performer Intelligent is optimized for maximum system efficiency (CELMA EEI A2 BAT) in combination with the TL5 and TL5 Eco lamp.

Product data

General Information		Mains voltage safety (AC)	
Application code	EII	Mains voltage safety (AC)	-10% - +10%
Type version	mk1	Earth leakage current (max.)	0.5 mA
Lamp type	TL5	Inrush current width	0.35 ms
Number of lamps	2 piece/unit	Constant wattage deviation	-2%/+2%
Number of products on MCB (16 A type B) (nom.)	12	Ballast factor (nom.)	1.00
Automatic restart	Yes	Power losses (nom.)	2.9-4.6 W
		Inrush current peak (max.)	31 A
Operating and Electrical		Wiring	
Input voltage	220 to 240 V	Connector type input terminals	Insert
Input frequency	50 to 60 Hz	Cable capacity output wires mutual (nom.)	70 pF
Ignition method	Warm Start	Connector type output terminals	Insert
Crest factor (max.)	1.7	Cable length hot-wiring	0.75 m
Ignition time (max.)	5.0 s	Wire strip length	8.0-9.0 mm
Mains voltage performance (AC)	-8% - +6%	Input terminal cross section	0.50-1.00 mm ²
		Output terminal cross section	0.50-1.00 mm ²

HF-Performer Intelligent for TL5 HE/HO lamps

Cable capacity output wires to earth (nom.)	70 pF
---	-------

System characteristics

Rated ballast-lamp power	14-39 W
Power loss on TL5 HO	3.6/4.6 W
Lamp power on TL5 HO	46.8/71.2 W
System power on TL5 HO	50.4/75.8 W
Rated lamp power on TL5 HO	24/39 W
Rated lamp power on TL5 HE	14/21 W
System power on TL5 HE	31.5/46.7 W
Lamp power on TL5 HE	28.6/42.8 W
Power loss on TL5 HE	2.9/3.9 W

Temperature

T ambient (max.)	50 °C
T ambient (min.)	-25 °C
T storage (max.)	80 °C
T storage (min.)	-40 °C
T case lifetime (nom.)	75 °C
T-Case maximum (max.)	75 °C
T-Ignition (max.)	50 °C
T-Ignition (min.)	-25 °C

Mechanical and Housing

Housing	L360x30x22
---------	------------

Emergency Operation

Nominal light output after 60 seconds	100% of EBLF
Battery voltage lamp operation	198-276
Emergency ballast lumen factor (EBLF) (nom.)	100 %
Nominal light output after 5 seconds	50% of EBLF


Approval and Application

Energy efficiency index	A2 BAT
IP classification	IP 20 [Ingress Protection 20]
EMI 9 kHz... 30 MHz	EN55015
EMI 30 MHz... 1,000 MHz	EN 55022 Class B
Safety standard	IEC 61347-2-3
Performance standard	IEC 60929
Quality standard	ISO 9000:2000
Environmental standard	ISO 14001
Harmonic current emission standard	IEC 61000-3-2
EMC immunity standard	IEC 61547
Vibration standard	IEC68-2-6 F c
Bumps standard	IEC 68-2-29 Eb
Humidity standard	EN 61347-2-3 clause 11
Approval marks	CE marking ENEC certificate VDE-EMV certificate
Temperature marking	Yes
Emergency standard	IEC 60598-2-22
Humming and noise level	Inaudible

Product Data

Full product code	871150091500930
Order product name	HF-Pi 2 14/21/24/39 TL5 EII 220-240V
EAN/UPC – product	8711500915009
Order code	91500930
Local Code	HFPi214212439
Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	913700624266
Net weight (piece)	0.290 kg

Dimensional drawing



HF-Pi 2 14/21/24/39 TL5 EII 220-240V

Product	D1	C1	A1	A2	B1
HF-Pi 2 14/21/24/39 TL5 EII 220-240V	4.2 mm	22 mm	360 mm	350 mm	30 mm

HF-Performer Intelligent for TL5 HE/HO lamps

