



HF-Performer Intelligent for TL5 HE/HO lamps

HF-Pi 2 28/35/49/54 TL5 EII 220-240V

HF-Performer Intelligent is a slim and lightweight high-frequency electronic ballast which makes it possible to exchange TL5 HE and HO lamps of the same length in order to maximize logistical flexibility in luminaire design and handling. With its smart power functionality based on Philips EII technology, HF-Performer Intelligent is optimized for maximum system efficiency (CELMA EEI A2 BAT) in combination with the TL5 and TL5 Eco lamp.

Product data


Operating and Electrical		T-Case Lifetime (Nom)		75 °C
Input Voltage	220 to 240 V	T-Case Maximum (Max)		75 °C
Line Frequency	50 to 60 Hz	Mechanical and Housing		
Input Frequency	50 to 60 Hz	Housing		L360x30x22
Earth Leakage Current (Max)	0.5 mA	Approval and Application		
Inrush Current Width	0.35 ms	Ingress protection code		IP20 [Finger-protected]
Inrush Current Peak (Max)	31 A	Energy Efficiency Index		A2 BAT
Number of Products on MCB (16A Type B) (Nom)	12	Safety Standard		IEC 61347-2-3
Wiring		Environmental Standard		ISO 14001
Connector Type Input Terminals	Insert	Approval Marks		CE marking ENEC certificate VDE-EMV certificate
Connector Type Output Terminals	Insert	Product Data		
Temperature		Order product name		HF-Pi 2 28/35/49/54 TL5 EII 220-240V
Ambient temperature range	-25 °C to 50 °C			

HF-Performer Intelligent for TL5 HE/HO lamps

Full product name	HF-Pi 2 28/35/49/54 TL5 EII 220-240V
Full product code	871150091502330
Order code	913700624366
Material Nr. (12NC)	913700624366
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8711500915023
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500915030

Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-Pi 2 28/35/49/54 TL5 EII 220-240V	4.2 mm	22 mm	360 mm	350 mm	30 mm

