



PrimaVision Power for CDM

HID-PV C 150 /I CDM 220-240V 50/60Hz


PrimaVision Power gear is designed for optimal performance of 100 and 150 W CDM lamps – ideal where high-intensity light is key.

Product data

Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing	/I
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		
Earth Leakage Current (Max)	350 mA		
Inrush Current Width	0.50 ms		
Inrush Current Peak (Max)	50 A		
Number of Products on MCB (16A Type B) (Nom)	6		
Wiring		Approval and Application	
Cable Length From Device to Lamp	2.0 m	Approval Marks	F-Marking CE marking ENEC certificate VDE-EMV certificate CB Certificate
Connector Type	Insert		
Temperature		Product Data	
Ambient temperature range	-20 °C to 45 °C	Order product name	HID-PV C 150 /I CDM 220-240V 50/60Hz
T-Case Lifetime (Nom)	70 °C	Full product name	HID-PV C 150 /I CDM 220-240V 50/60Hz
T-Case Maximum (Max)	80 °C	Full product code	871150091287930
		Order code	913700624466
		Material Nr. (12NC)	913700624466
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500912879
		Numerator - Packs per outer box	10
		EAN/UPC - Case	8711500912886

PrimaVision Power for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV C 150 /1 CDM 220-240V 50/60Hz	4.8 mm	34.2 mm	223.9 mm	206.0 mm	82.7 mm

