



HID ignitors for series systems

SX 73 220-240V 50/60HZ

HID ignitors for series systems

Product data


General Information	
Application code	73
Lamp type	SOX
Number of lamps	1 piece/unit
Operating and Electrical	
Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Ignition type	Parallel
Ignition voltage (max.)	1.4 kV
Response voltage	198 V
Mains voltage performance (AC)	-8% - +6%
Mains voltage safety (AC)	-10% - +10%
Power losses (nom.)	1.0 W
Wiring	
Cable capacity wires device to lamp (nom.)	5 nF
Wire strip length	6.0 mm
Ballast contact wire cross section	0.50-2.50 mm ²
Connector type	Screw

System characteristics	
Rated ballast-lamp power	180 W
Temperature	
T ambient (max.)	75 °C
T ambient (min.)	-20 °C
T storage (max.)	80 °C
T storage (min.)	-25 °C
T-Case maximum (max.)	80 °C
Mechanical and Housing	
Housing	SNI-85
Approval and Application	
Approval marks	CE marking ENEC certificate
Product Data	
Full product code	871150092005830
Order product name	SX 73 220-240V 50/60Hz
EAN/UPC – product	8711500920058
Order code	92005830
Local Code	SX73
Numerator – quantity per pack	1

HID ignitors for series systems

Numerator – packs per outer box	48
Material no. (12NC)	913700625466
Net weight (piece)	0.060 kg

Dimensional drawing



Product	C1	A1	B1
SX 73 220-240V 50/60Hz	38.5 mm	85.5 mm	41.5 mm

SX 73 220-240V 50/60Hz

