



Primaline Halogen Transformers

PRIMALINE 105 230-240V 50/60HZ

High-Frequency electronic transformer for operation with 12V halogen lamps, available in 70W, 105W and 150W versions

Warnings and Safety

 \cdot Transformer is not suitable for DC operation

Product data


Operating and Electrical				
Input Voltage	230 to 240 V			
Line Frequency	50 to 60 Hz			
Input Frequency	50 to 60 Hz			
Temperature				
T-Case Lifetime (Nom)	65 ℃			
T-Case Maximum (Max)	80 ℃			
Approval and Application				
Approval Marks	SELV CE marking ENEC certificate			

Product Data	
Order product name	Primaline 105 230-240V 50/60Hz
Full product name	PRIMALINE 105 230-240V 50/60HZ
Full product code	871150091268830
Order code	91268830
Material Nr. (12NC)	913700627691
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500912688
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500912695

Datasheet, 2023, April 30 data subject to change

Primaline Halogen Transformers

Dimensional drawing



Product	C1	A1	B1
Primaline 105 230-240V 50/60Hz	33 mm	110 mm	45 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.