



# HF-Performer II for PL-T/C/R/L/TL5C lamps

## HF-P 1 13-17 PL-T/C/R EII 220-240V

HF-Performer EII PL-T/C/R/T5c is a sustainable, slim and high-frequency electronic ballast for a wide range of CFL- ni applications. It is ideal for applications where high energy efficiency is required. The HF-Performer EII range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2).

### Product data

| Operating and Electrical                     |                 |
|----------------------------------------------|-----------------|
| Input Voltage                                | 220 to 240 V    |
| Line Frequency                               | 50 to 60 Hz     |
| Input Frequency                              | 50 to 60 Hz     |
| Inrush Current Width                         | 0.25 ms         |
| Inrush Current Peak (Max)                    | 18 A            |
| Number of Products on MCB (16A Type B) (Nom) | 28              |
| Wiring                                       |                 |
| Connector Type Input Terminals               | Insert          |
| Connector Type Output Terminals              | Insert          |
| Temperature                                  |                 |
| Ambient temperature range                    | -25 °C to 50 °C |
| T-Case Lifetime (Nom)                        | 75 °C           |


| T-Case Maximum (Max)     | 75 °C                                           |
|--------------------------|-------------------------------------------------|
| Approval and Application |                                                 |
| Ingress protection code  | IP20 [Finger-protected]                         |
| Energy Efficiency Index  | A2                                              |
| Safety Standard          | IEC 61347-2-3                                   |
| Environmental Standard   | ISO 14001                                       |
| Approval Marks           | CE marking ENEC certificate VDE-EMV certificate |

| Product Data                  |                                    |
|-------------------------------|------------------------------------|
| Order product name            | HF-P 1 13-17 PL-T/C/R EII 220-240V |
| Full product name             | HF-P 1 13-17 PL-T/C/R EII 220-240V |
| Full product code             | 871150091407130                    |
| Order code                    | 913700631166                       |
| Material Nr. (12NC)           | 913700631166                       |
| Numerator - Quantity Per Pack | 1                                  |

HF-Performer II for PL-T/C/R/L/TL5C lamps

|                                 |               |
|---------------------------------|---------------|
| EAN/UPC - Product/Case          | 8711500914071 |
| Numerator - Packs per outer box | 12            |
| EAN/UPC - Case                  | 8711500914088 |

Dimensional drawing



| Product                              | D1     | C1      | A1       | A2      | B1      | B2      |
|--------------------------------------|--------|---------|----------|---------|---------|---------|
| HF-P 113-17 PL-T/C/R EII<br>220-240V | 4.5 mm | 30.0 mm | 103.0 mm | 93.5 mm | 67.0 mm | 57.5 mm |

