



# Certaline Halogen Transformers

## CERTALINE 150W 230-240V 50/60HZ

Electronic halogen transformer for low voltage halogen lamps the range include Certaline 60W 230-240V and Certaline105W 230-240V

### Warnings and Safety

- Transformer is not suitable for DC operation


### Product data

Operating and Electrical	
Input Voltage	230 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Temperature	
T-Case Lifetime (Nom)	65 °C
T-Case Maximum (Max)	75 °C
Approval and Application	
Approval Marks	SELV CE marking VDE marking

Product Data	
Order product name	Certaline 150W 230-240V 50/60Hz
Full product name	CERTALINE 150W 230-240V 50/60HZ
Full product code	871150091385230
Order code	91385230
Material Nr. (12NC)	913700634091
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500913852
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500913869

# Certaline Halogen Transformers

## Dimensional drawing



Product	C1	A1	B1
Certaline 150W 230-240V 50/60Hz	36.0 mm	180.0 mm	46.0 mm

