



e-Vision Low Wattage 20-150W

E-VISION ELE MH BAL 39W M130/C179 120V 50/60HZ

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

Product data


General Information		Input Power (Nom)	
ANSI Code	C130-M130,C179	Rated Lamp Power	45 W
Lamp Type	39W MH		39 W
Number of Lamps	1 piece/unit	Wiring	
Ballast Type	Electronic HID	Color Input Terminals	No terminals
Base Model	RMH39KBL5	Color Output Terminals	No terminals
Suitable For Outdoor Use	Yes	Wire Striplength	0.50 mm
Operating and Electrical		Control Wire Gauge	NA
Input Voltage	120 V	Wire Length by Color	All leads = 6"
Input Frequency	50 to 60 Hz	Wire Gauge (Nom)	18AWG mm
Total Harmonic Distortion USA	15 %	Wire Type	Stranded
Crestfactor (Nom)	1.8	Remote Wiring Configuration Allowed	Yes
Ignition Time (Nom)	1200 s	Tandem Wiring Configuration Allowed	No
Ballast Factor (Nom)	1	Through Wiring Configuration Allowed	No
Power Factor (Nom)	0.90	Connector Type	No connector
Input Current (Max)	0.4 A		
Input Current (Min)	0.4 A		

e-Vision Low Wattage 20-150W

Temperature	
T-Case Maximum (Nom)	90 °C
Mechanical and Housing	
Housing Material	Metal
Housing	K
Housing Dimensions	4.1" x 1.3" x 1.2"
Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate RoHS Compliant
Hum And Noise Level	A
UL Recognized	No

Product Data	
Order product name	E-VISION ELE MH BAL 39W M130/C179 120V 50/60HZ
EAN/UPC - Product	781087073193
Order code	107367
Local order code	107367
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913700639089
Net Weight (Piece)	196.000 g

Dimensional drawing



E-VISION RMH39KBLSM

Product	A1	A2	A3	B1	B2	C1
E-VISION ELE MH BAL 39W M130/C179 120V 50/60HZ	4.4 in	4.1 in	4.5 in	1.1 in	0.5 in	1.2 in

