



# AspiraVision Compact for CDM

## HID-AV C 35 /C CDM 220-240V 50/60Hz

AspiraVision is the mark of excellence in HID electronic gear technology – high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps. The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver.

### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	500 mA
Input Current (Nom)	0.23 A
Wiring	
Connector Type	Wieland
Temperature	
Ambient temperature range	-20 °C to 55 °C
Controls and Dimming	
Control Interface	-
Mechanical and Housing	
Housing	/C

Approval and Application	
Surge Protection (Common/Differential)	EN61547 (L-L 1kV, L-G 2kV) kV
Approval Marks	F-Marking CE marking ENEC certificate VDE certificate CB Certificate VDE-EMC marking
Product Data	
Order product name	HID-AV C 35 /C CDM 220-240V 50/60Hz
Full product name	HID-AV C 35 /C CDM 220-240V 50/60Hz
Full product code	872790088525500
Order code	913700647966
Material Nr. (12NC)	913700647966
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500881670
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900885255

# AspiraVision Compact for CDM

## Dimensional drawing

Product	D1	C1	A1	A2	B1
HID-AV C 35 /C CDM 220-240V 50/60Hz	4.8 mm	32.4 mm	162.2 mm	143 mm	83.0 mm

