



# PrimaVision Power for CDM

## HID-PV C 100 /S CDM 220-240V 50/60Hz

PrimaVision Power gear is designed for optimal performance of 100 and 150 W CDM lamps – ideal where high-intensity light is key.


### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.25 mA
Inrush Current Width	0.40 ms
Inrush Current Peak (Max)	40 A
Number of Products on MCB (16A Type B) (Nom)	17
Wiring	
Cable Length From Device to Lamp	2 m
Connector Type	Insert
Temperature	
Ambient temperature range	-20 °C to 50 °C
T-Case Lifetime (Nom)	75 °C
T-Case Maximum (Max)	75 °C
Mechanical and Housing	
Housing	/S

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Safety Standard	EN60928, 60926
Environmental Standard	ISO 14001
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	HID-PV C 100 /S CDM 220-240V 50/60Hz G5
Full product name	HID-PV C 100 /S CDM 220-240V 50/60Hz
Full product code	872790089762300
Order code	89762300
Material Nr. (12NC)	913700656266
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500881830
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900897623

# PrimaVision Power for CDM

## Dimensional drawing



Product	A1	A2	B1	B2	C1	D1
HID-PV C 100 /S CDM 220-240V 50/60Hz G5	135.0 mm	123.5 mm	75.0 mm	63.5 mm	32.0 mm	4.5 mm

