



PrimaVision for SDW-TG

HID-PV 50 /S SDW-TG 220-240V 50/60Hz


Robust, lightweight and one-piece HID electronic gear for SDW-TG lamps (mini White SON) Lightweight, one-piece electronic gear for 50 and 100 W SDW-TG lamps (mini White SON)

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	0.35 ms
Inrush Current Peak (Max)	24 A
Number of Products on MCB (16A Type B) (Nom)	24
Wiring	
Cable Length From Device to Lamp	2 m
Connector Type	Insert
Temperature	
Ambient temperature range	-20 °C to 60 °C
T-Case Lifetime (Nom)	75 °C
T-Case Maximum (Max)	85 °C

Mechanical and Housing	
Housing	/S
Approval and Application	
Approval Marks	CE marking ENEC certificate CB Certificate
Product Data	
Order product name	HID-PV 50 /S SDW-TG 220-240V 50/60Hz
Full product name	HID-PV 50 /S SDW-TG 220-240V 50/60Hz
Full product code	872790088753200
Order code	88753200
Material Nr. (12NC)	913700656666
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500881878
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900887532

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV 50 /S SDW-TG 220-240V 50/60Hz	4.5 mm	37.0 mm	150.0 mm	133.6 mm	90.0 mm	70.0 mm

