



HF-Performer Intelligent for TL5 HE/HO lamps

HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V

HF-Performer Intelligent for Master and ECO TL5 HE/HO, TL-D and PL-L lamps. HF-Performer Intelligent features automatic recognition of the connected lamp and is independently able to adjust its operation parameters exactly to the respective lamp. This results in a substantial benefit, especially for T5 lamps, as it means TL5 HE and HO lamps of the same length can be interchanged. With a choice of seven ballasts, the customer is able to handle efficiently every possible combination of Master TL5 and Eco, TL-D, and PL-L lamps.

Product data


Operating and Electrical		Temperature	
Input Voltage	220 to 240 V	Ambient temperature range	-25 °C to 50 °C
Line Frequency	50 to 60 Hz	T-Case Lifetime (Nom)	75 °C
Input Frequency	50 to 60 Hz	T-Case Maximum (Max)	75 °C
Earth Leakage Current (Max)	0.5 mA	Mechanical and Housing	
Inrush Current Width	0.4 ms	Housing	L360x30x22
Inrush Current Peak (Max)	45 A	Approval and Application	
Number of Products on MCB (16A Type B) (Nom)	12	Energy Efficiency Index	A2 BAT
Wiring		Safety Standard	IEC 61347-2-3
Connector Type Input Terminals	Insert	Environmental Standard	ISO 14001
Connector Type Output Terminals	Insert	Approval Marks	CE marking ENEC certificate VDE-EMV certificate
Cable Length From Device to Lamp	2 m		

HF-Performer Intelligent for TL5 HE/HO lamps

Product Data	
Order product name	HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V
Full product name	HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V
Full product code	872790088775400
Order code	88775400
Material Nr. (12NC)	913700657666

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500881960
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900887754

Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V	4.2 mm	22 mm	360 mm	350 mm	30 mm

