



HF-Performer Intelligent for TL5 HE/HO lamps

HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V

HF-Performer Intelligent is a slim and lightweight high-frequency electronic ballast which makes it possible to exchange TL5 HE and HO lamps of the same length in order to maximize logistical flexibility in luminaire design and handling. With its smart power functionality based on Philips EII technology, HF-Performer Intelligent is optimized for maximum system efficiency (CELMA EEI A2 BAT) in combination with the TL5 and TL5 Eco lamp.

Product data


Operating and Electrical		Temperature	
Input Voltage	220 to 240 V	Ambient temperature range	-25 °C to 50 °C
Line Frequency	50 to 60 Hz	T-Case Lifetime (Nom)	75 °C
Input Frequency	50 to 60 Hz	T-Case Maximum (Max)	75 °C
Earth Leakage Current (Max)	0.5 mA	Mechanical and Housing	
Inrush Current Width	0.4 ms	Housing	L360x30x22
Inrush Current Peak (Max)	45 A	Approval and Application	
Number of Products on MCB (16A Type B) (Nom)	12	Energy Efficiency Index	A2 BAT
Wiring		Safety Standard	IEC 61347-2-3
Connector Type Input Terminals	Insert	Environmental Standard	ISO 14001
Connector Type Output Terminals	Insert	Approval Marks	CE marking ENEC certificate VDE-EMV certificate
Cable Length From Device to Lamp	2 m		

HF-Performer Intelligent for TL5 HE/HO lamps

Product Data	
Order product name	HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V
Full product name	HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V
Full product code	872790088775400
Order code	913700657666
Material Nr. (12NC)	913700657666

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500881960
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900887754

Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-Pi 3/4 14/24 TL5/PL-L EII 220-240V	4.2 mm	22 mm	360 mm	350 mm	30 mm

