



PrimaVision Xtreme for CPO

HID-PV Xt 210 CDMe/CPO C2 208-277V

Highly reliable electronic drivers for CPO lamps; designed to save energy by offering better light efficiency than magnetic drivers and to reduce maintenance costs thanks to 80,000-hour lifetime and integrated lightning protection

Product data

Operating and Electrical	
Input Voltage	208-240-277 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.7 mA
Inrush Current Width	4 ms
Input Current (Nom)	1.11 A
Inrush Current Peak (Max)	4 A
Number of Products on MCB (16A Type B) (Nom)	13
Wiring	
Cable Length From Device to Lamp	3 m
Connector Type	WAGO series 804
Temperature	
Ambient temperature range	-30 °C to 50 °C
T-Case Lifetime (Nom)	80 °C


Mechanical and Housing	
Housing	C2
Approval and Application	
Surge Protection (Common/Differential)	EN61547 (L-L 2kV, L-G 4kV), 10 kV TIL
Safety Standard	IEC 607, 609, 926, 928 [No Standard for HID Lamp drivers exists. Requirements in these standards to be used if considered relevant for the product.]
Environmental Standard	ISO 14001
Approval Marks	F-Marking CE marking ENEC certificate VDE-EMV certificate

Product Data	
Order product name	HID-PV Xt 210 CDMe/CPO C2 208-277V
Full product name	HID-PV Xt 210 CDMe/CPO C2 208-277V
Full product code	871829121993400
Order code	913700672766
Material Nr. (12NC)	913700672766
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291219934
Numerator - Packs per outer box	6

PrimaVision Xtreme for CPO

EAN/UPC - Case	8718291219941
----------------	---------------

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV Xt 210	4.8 mm	58.0 mm	169.0 mm	156.0 mm	100.0 mm	81.5 mm
CDMe/CPO C2 208-277V						

