



DynaVision Programmable Xtreme for SON

HID-DV PROG Xt 100 SON C1 208-277V

Highly reliable and flexible electronic drivers for SON lamps; designed to save energy via integrated controls, and to reduce maintenance costs thanks to 80,000-hour lifetime and integrated lightning protection. The DynaVision Programmable product family is the perfect basis for any sort of lighting management solution.

Produktdata


Drift og elektronikk		
Inngangsspenning	208-240-277 V	
Line Frequency	50 to 60 Hz	
Inngangsfrekvens	50 til 60 Hz	
Jordlekkasjestrøm (maks.)	0,7 mA	
Startstrøm-bredde	0,47 ms	
Inngangsstrøm (nom.)	0.53 A	
Startstrøm-topp (nom.)	52 A	
Antall produkter på MCB (16A type B) (nom.)	5	
Kabling		
Kabellengde fra enhet til lyskilde	10 m	
Tilkoblingstype	WAGO-serien 804	
Temperatur		
Omgivelsestemperatur	-30 °C til 50 °C	
Temperatur for optimal levetid for forkoblingsinnfatningen (nom.)		80 °C
Kontroller og dimming		
Kontrollgrensesnitt	PROG	
Mekanikk og innfatning		
Armaturhus	C1	
Godkjenning og bruksområde		
Surge Protection (Common/Differential)	EN61547 (L-L 2 kV, L-G 4 kV), 10 kV TIL	
Sikkerhetsstandard	IEC 607, 609, 926, 928 [Det finnes ingen standard for HID-lampedrivere. Krav i disse standardene skal brukes hvis de anses som relevante for produktet.]	
Miljøstandard	ISO 14001	

DynaVision Programmable Xtreme for SON

Godkjenningsmerker	F-merking CE-merking VDE-EMV-sertifikat ENEC-sertifikat
Produktdata	
Produktnavn for bestilling	HID-DV PROG Xt 100 SON C1 208-277V
Fullstendig produktnavn	HID-DV PROG Xt 100 SON C1 208-277V
Full EOC	871829121224900
Lokal kodebeskrivelse	3381874
Bestillingskode	21224900

Materialenr. (12NC)	913700678766
Lokal bestillingskode	3381874
SAP-teller – antall per pakke	1
EAN/UPC – produkt/boks	8718291212249
SAP-teller – pakker per utvendige	12
EAN/UPC – boks	8718291212256

Målskisse



Product	D1	C1	A1	A2	B1	B2
HID-DV PROG Xt 100 SON C1 208-277V	5,0 mm	65,0 mm	150,0 mm	135,9 mm	65,0 mm	46,8 mm

