



# DynaVision Programmable Xtreme for SON

## HID-DV PROG Xt 150 SON C1 208-277V

Highly reliable and flexible electronic drivers for SON lamps; designed to save energy via integrated controls, and to reduce maintenance costs thanks to 80,000-hour lifetime and integrated lightning protection. The DynaVision Programmable product family is the perfect basis for any sort of lighting management solution.

### Produktdata

|                                             |                  |
|---------------------------------------------|------------------|
| <b>Drift og elektronikk</b>                 |                  |
| Inngangsspenning                            | 208-240-277 V    |
| Line Frequency                              | 50 to 60 Hz      |
| Inngangsfrekvens                            | 50 til 60 Hz     |
| Jordlekkasjestrøm (maks.)                   | 0,7 mA           |
| Startstrøm-bredde                           | 0,47 ms          |
| Inngangsstrøm (nom.)                        | 0,77 A           |
| Startstrøm-topp (nom.)                      | 52 A             |
| Antall produkter på MCB (16A type B) (nom.) | 5                |
| <b>Kabling</b>                              |                  |
| Kabellengde fra enhet til lyskilde          | 10 m             |
| Tilkoblingstype                             | WAGO-serien 804  |
| <b>Temperatur</b>                           |                  |
| Omgivelsestemperatur                        | -30 °C til 50 °C |


|                                                                   |                                                                                                                                                          |
|-------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Temperatur for optimal levetid for forkoblingsinnfatningen (nom.) | 80 °C                                                                                                                                                    |
| <b>Kontroller og dimming</b>                                      |                                                                                                                                                          |
| Kontrollgrensesnitt                                               | PROG                                                                                                                                                     |
| <b>Mekanikk og innfatning</b>                                     |                                                                                                                                                          |
| Armaturhus                                                        | C1                                                                                                                                                       |
| <b>Godkjenning og bruksområde</b>                                 |                                                                                                                                                          |
| Surge Protection (Common/Differential)                            | EN61547 (L-L 2 kV, L-G 4 kV), 10 kV TIL                                                                                                                  |
| Sikkerhetsstandard                                                | IEC 607, 609, 926, 928 [Det finnes ingen standard for HID-lampedrivere. Krav i disse standardene skal brukes hvis de anses som relevante for produktet.] |
| Miljøstandard                                                     | ISO 14001                                                                                                                                                |

# DynaVision Programmable Xtreme for SON

|                            |                                                            |
|----------------------------|------------------------------------------------------------|
| Godkjenningsmerker         | F-merking CE-merking ENEC-sertifikat<br>VDE-EMV-sertifikat |
| Produktdata                |                                                            |
| Produktnavn for bestilling | HID-DV PROG Xt 150 SON C1 208-277V                         |
| Fullstendig produktnavn    | HID-DV PROG Xt 150 SON C1 208-277V                         |
| Full EOC                   | 871829121226300                                            |
| Lokal kodebeskrivelse      | 3381871                                                    |
| Bestillingskode            | 21226300                                                   |

|                                   |               |
|-----------------------------------|---------------|
| Materialenr. (12NC)               | 913700678866  |
| Lokal bestillingskode             | 3381871       |
| SAP-teller – antall per pakke     | 1             |
| EAN/UPC – produkt/boks            | 8718291212263 |
| SAP-teller – pakker per utvendige | 12            |
| EAN/UPC – boks                    | 8718291212270 |

## Målskisse



| Product                               | D1     | C1      | A1       | A2       | B1      | B2      |
|---------------------------------------|--------|---------|----------|----------|---------|---------|
| HID-DV PROG Xt 150 SON<br>C1 208-277V | 5,0 mm | 65,0 mm | 150,0 mm | 135,9 mm | 65,0 mm | 46,8 mm |

