




AspiraVision Compact for CDM

HID-AV C 35-70 /I CDM 220-240V 50/60Hz


AspiraVision is the mark of excellence in HID electronic gear technology – high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps. The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver.

产品数据

操作和电气	
输入电压	220 至 240 V
线频率	50 to 60 Hz
输入频率	50 至 60 Hz
对地漏电流 (最大)	250 mA
侵入电流宽度	10 ms
侵入电流峰值 (最大)	8 A
MCB 上的产品数量 (16A 类型 B)(标称) 58	
布线	
从设备到灯具的电缆长度	2 m
连接器类型	WAGO 804 系列
温度	
环境温度范围	-20 °C 至 45 °C
外壳温度使用寿命 (标称)	80 °C
控制和调光	
控制接口	-

机械和外壳	
外壳	/I
审批和申请	
浪涌保护 (通用/差异)	EN61547 (L-L 2kV , L-G 4kV) kV
安全标准	EN 61347-2-12 和 2-1
批准标志	EMC HEE F 标记 CE 标记 ENEC 证书 VDE 证书 CB 证书 VDE 标记 C-Tick 证书 中国质量证书
产品数据	
订单产品名称	HID-AV C 35-70 /I CDM 220-240V 50/60Hz
完整的产品名称	HID-AV C 35-70 /I CDM 220-240V 50/60Hz
完整产品代码	871829123312100
订购代码	913700684066
材料编号 (12NC)	913700684066
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8718291233121
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8718291233138

二维绘图



Product	D1	C1	A1	A2	B1
HID-AV C 35-70 /I CDM 220-240V 50/60Hz	4.8 mm	34.7 mm	189.2 mm	170.7 mm	83.5 mm

