



HF-Regulator Intelligent Touch DALI for PL-T/C and TL5C

HF-Ri TD 1 26-42 PL-T/C E+

Intelligent high-frequency electronic dimming ballast, using DALI (Digital Addressable Lighting Interface according to IEC62386) or Touch and Dim push-button protocol for fluorescent lamps. Features Corridor Mode, programmable with Philips MultiOne. High-frequency operation improves light quality and lamp lifetime. Pre-empts upcoming legislation as it meets A1BAT requirements.

产品数据

操作和电气	
输入电压	195–240 V
线频率	50 to 60 Hz
输入频率	50 至 60 Hz
对地漏电流 (最大)	0.5 mA
侵入电流宽度	0.35 ms
侵入电流峰值 (最大)	27 A
MCB 上的产品数量 (16A 类型 B) (标称)	28
布线	
连接器类型输入端子	WAGO 250 系列
连接器类型输出端子	WAGO 250 系列
温度	
环境温度范围	–25 °C 至 50 °C
外壳温度使用寿命 (最大)	75 °C


最大外壳温度 (最大)	75 °C
控制和调光	
控制接口	TD
机械和外壳	
外壳	L 123x79x33
审批和申请	
IP 等级	IP20 [手指保护]
能效指数	A1 BAT
安全标准	IEC 61347–2–3
环保标准	ISO 14001
批准标志	EMC CE 标记 ENEC 证书 CCC
产品数据	
订单产品名称	HF-Ri TD 1 26-42 PL-T/C E+

HF-Regulator Intelligent Touch DALI for PL-T/C and TL5C

完整的产品名称	HF-Ri TD 1 26-42 PL-T/C E+
完整产品代码	871829124167600
订购代码	913700684766
材料编号 (12NC)	913700684766
计算器 - 每包数量	1

EAN/UPC - 产品/箱	8718291241676
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8718291241683

二维绘图



Product	D1	C1	A1	A2	B1	B2
HF-Ri TD 1 26-42 PL-T/C E	4.5 mm	33.0 mm	123.0 mm	111.0 mm	79.0 mm	67.0 mm
+						

