



# PrimaVision Xtreme for CPO

## HID-PV Xt 140 CPO L1 208-277V

Compact, robust, outdoor, one-piece, electronic ballasts for CosmoPolis White (CPO-TW) lamps

### Product data


| Operating and Electrical                     |                 |
|--|-----------------|
| Input Voltage                                | 208-240-277 V   |
| Line Frequency                               | 50 to 60 Hz     |
| Input Frequency                              | 50 to 60 Hz     |
| Earth Leakage Current (Max)                  | 0.7 mA          |
| Inrush Current Width                         | 0.47 ms         |
| Input Current (Nom)                          | 0.75 A          |
| Inrush Current Peak (Max)                    | 52 A            |
| Number of Products on MCB (16A Type B) (Nom) | 5               |
| Wiring                                       |                 |
| Cable Length From Device to Lamp             | 10 m            |
| Connector Type                               | WAGO series 804 |
| Temperature                                  |                 |
| Ambient temperature range                    | -30 °C to 55 °C |
| T-Case Lifetime (Nom)                        | 80 °C           |
| Mechanical and Housing                       |                 |
| Housing                                      | Q               |

| Approval and Application               |  |
|--|--|
| Surge Protection (Common/Differential) | EN61547 (L-L 2kV, L-G 4kV), 10 kV TIL  |
| Safety Standard                        | IEC 607, 609, 926, 928 [No Standard for HID Lamp drivers exists. Requirements in these standards to be used if considered relevant for the product.] |
| Environmental Standard                 | ISO 14001  |
| Approval Marks                         | F-Marking CE marking ENEC certificate VDE-EMV certificate  |

| Product Data                    |                               |
|---------------------------------|-------------------------------|
| Order product name              | HID-PV Xt 140 CPO Q 208-277V  |
| Full product name               | HID-PV Xt 140 CPO L1 208-277V |
| Full product code               | 871829124147800               |
| Order code                      | 24147800                      |
| Material Nr. (12NC)             | 913700685666                  |
| Numerator - Quantity Per Pack   | 1                             |
| EAN/UPC - Product/Case          | 8718291241478                 |
| Numerator - Packs per outer box | 12                            |
| EAN/UPC - Case                  | 8718291241485                 |

PrimaVision Xtreme for CPO

Dimensional drawing



| Product                         | D1     | C1      | A1       | A2       | B1      | B2      |
|---------------------------------|--------|---------|----------|----------|---------|---------|
| HID-PV Xt 140 CPO Q<br>208-277V | 4.5 mm | 40.0 mm | 150.0 mm | 133.6 mm | 90.0 mm | 70.0 mm |

