



HF-Regulator Intelligent Touch DALI for TL5/TL-D/PL-L lamps

HF-Ri TD 2 28/35/49/54 TL5 E+ 195-240V

This intelligent high-frequency electronic dimming ballast utilizes the DALI or Touch and Dim push-button protocol for fluorescent lamps. It meets A1BAT requirements, thereby pre-empting upcoming legislation. With a special command you can retrieve the system's mains power consumption, and with another you can find out which lamp wattage is connected. Combined with controls, additional energy savings can be achieved.

产品数据

操作和电气		连接器类型输出端子	
输入电压	195-240 V	WAGO 251 通用连接器 [适用于自动连线 (ALF 和 ADS) 和手动连线]	
纹频率	50 to 60 Hz		
输入频率	50 至 60 Hz	温度	
对地漏电流 (最大)	0.5 mA	环境温度范围	-25 °C 至 50 °C
侵入电流宽度	0.25 ms	外壳温度使用寿命 (最大)	75 °C
侵入电流峰值 (最大)	28 A	最大外壳温度 (最大)	75 °C
MCB 上的产品数量 (16A 类型 B)(标称)	18		
		控制和调光	
布线		控制接口	TD
连接器类型输入端子	WAGO 251 通用连接器 [适用于自动连线 (ALF 和 ADS) 和手动连线]		


HF-Regulator Intelligent Touch DALI for TL5/TL-D/PL-L lamps

机械和外壳	
外壳	L 359x30x21
审批和申请	
IP 等级	IP20 [手指保护]
能效指数	A1 BAT
安全标准	IEC 61347-2-3
环保标准	ISO 14001
批准标志	CE 标志 ENEC 证书 VDE-EMV 证书

产品数据	
订单产品名称	HF-Ri TD 2 28/35/49/54 TL5 E+ 195-240V

完整的产品名称	HF-Ri TD 2 28/35/49/54 TL5 E+ 195-240V
完整产品代码	871829166209900
订购代码	913700695866
材料编号 (12NC)	913700695866
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8718291662099
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8718291662105

二维绘图



Product	D1	C1	A1	A2	B1
HF-Ri TD 2 28/35/49/54 TL5 E+ 195-240V	4.1 mm	22.0 mm	360.0 mm	350.0 mm	30.0 mm

