

PrimaVision Mini for CDM

HID-PV m PGJ5 35 /I CDM 220-240V 50/60Hz


Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

Product data

Operating and Electrical		Approval and Application	
Input Voltage	220 to 240 V	Approval Marks	F-Marking CE marking CB Certificate
Line Frequency	50 to 60 Hz	Product Data	
Input Frequency	50 to 60 Hz	Full product code	871829169398700
Earth Leakage Current (Max)	0.25 mA	Order product name	HID-PV m PGJ5 35 /I CDM 220-240V 50/60Hz
Inrush Current Width	0.25 ms	Order code	913700698266
Inrush Current Peak (Max)	15 A	Numerator - Quantity Per Pack	1
Number of Products on MCB (16A Type B) (Nom)	24	Numerator - Packs per outer box	10
Wiring		Material Nr. (12NC)	913700698266
Cable Length From Device to Lamp	2 m	Full product name	HID-PV m PGJ5 35 /I CDM 220-240V 50/60Hz
Connector Type	Insert	EAN/UPC - Case	8718291693994
Temperature		EAN/UPC - Product/Case	8718291693987
Ambient temperature range	-20 °C to 45 °C		
T-Case Lifetime (Nom)	80 °C		
T-Case Maximum (Max)	85 °C		
Mechanical and Housing			
Housing	/I		

PrimaVision Mini for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV m PGJ5 35 /I CDM 220-240V 50/60Hz	4.8 mm	34 mm	234.7 mm	225.0 mm	49.3 mm

