

Gear for SDW-T lamps

BSL 100 K202-A2-TS 230V 50Hz

CSLS electronic control unit with impregnated (HID 'BASIC') or encapsulated (HID 'Heavy Duty') electromagnetic ballasts

Warnings and Safety


- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)

Product data

Operating and Electrical		Full product name		BSL 100 K202-A2-TS 230V 50Hz	
Input Voltage	230 V	Full product code		871869674076700	
Line Frequency	50 Hz	Order code		913700751826	
Input Frequency	50 Hz	Material Nr. (12NC)		913700751826	
		Numerator - Quantity Per Pack		1	
		EAN/UPC - Product/Case		8718696740767	
		Numerator - Packs per outer box		6	
		EAN/UPC - Case		8718696740774	
Approval and Application					
Approval Marks	CE marking ENEC certificate				
Product Data					
Order product name	BSL 100 K202-A2-TS 230V 50Hz				

Gear for SDW-T lamps

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSL 100 K202-A2-TS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm

