

# HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

## BSN 100 K302-A2-ITS 230V 50Hz


Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BSN 100 K302-A2-ITS 230V 50Hz	
Input Voltage	230 V	<b>Full product code</b>		871869674086600	
Line Frequency	50 Hz	<b>Order code</b>		913700752326	
Input Frequency	50 Hz	<b>Material Nr. (12NC)</b>		913700752326	
		<b>Numerator - Quantity Per Pack</b>		1	
		<b>EAN/UPC - Product/Case</b>		8718696740866	
		<b>Numerator - Packs per outer box</b>		6	
		<b>EAN/UPC - Case</b>		8718696740873	
<b>Wiring</b>					
Connector Type	Screw				
<b>Approval and Application</b>					
Approval Marks	CE marking ENEC certificate				
<b>Product Data</b>					
Order product name	BSN 100 K302-A2-ITS 230V 50Hz				

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 100 K302-A2-ITS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm

