

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 100 K202-A2-TS-R 230V 50Hz


Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name		BSN 100 K202-A2-TS-R 230V 50Hz	
Input Voltage	230 V	Full product code		871869674088000	
Line Frequency	50 Hz	Order code		913700752426	
Input Frequency	50 Hz	Material Nr. (12NC)		913700752426	
		Numerator - Quantity Per Pack		1	
		EAN/UPC - Product/Case		8718696740880	
		Numerator - Packs per outer box		6	
		EAN/UPC - Case		8718696740897	
Approval and Application					
Approval Marks		CE marking ENEC certificate			
Product Data					
Order product name		BSN 100 K202-A2-TS-R 230V 50Hz			

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 100 K202-A2-TS-R 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm

