



HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 150 K202-A2-TS-R 230V 50Hz

Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

| | | | | | |
|---------------------------------|--------------------------------|--|--|--------------------------------|--|
| Operating and Electrical | | Full product name | | BSN 150 K202-A2-TS-R 230V 50Hz | |
| Input Voltage | 230 V | Full product code | | 871869674098900 | |
| Line Frequency | 50 Hz | Order code | | 913700752726 | |
| Input Frequency | 50 Hz | Material Nr. (12NC) | | 913700752726 | |
| | | Numerator - Quantity Per Pack | | 1 | |
| | | EAN/UPC - Product/Case | | 8718696740989 | |
| | | Numerator - Packs per outer box | | 6 | |
| | | EAN/UPC - Case | | 8718696740996 | |
| | | | | | |
| Approval and Application | | | | | |
| Approval Marks | CE marking ENEC certificate | | | | |
| | | | | | |
| Product Data | | | | | |
| Order product name | BSN 150 K202-A2-TS-R 230V 50Hz | | | | |

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



| Product | A1 | A2 | B1 | C1 | D1 |
|--------------------------------|--------|--------|-------|-------|--------|
| BSN 150 K202-A2-TS-R 230V 50Hz | 134 mm | 113 mm | 76 mm | 65 mm | 6.2 mm |

