



HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 250 K302-A2-ITS 230V 50Hz



Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name	
Input Voltage	230 V	BSN 250 K302-A2-ITS 230V 50Hz	
Line Frequency	50 Hz	Full product code	871869674102300
Input Frequency	50 Hz	Order code	74102300
Wiring		Material Nr. (12NC)	913700752926
Connector Type	Screw	Numerator - Quantity Per Pack	1
Approval and Application		EAN/UPC - Product/Case	8718696741023
Approval Marks	CE marking ENEC certificate	Numerator - Packs per outer box	6
Product Data		EAN/UPC - Case	8718696741030
Order product name	BSN 250 K302-A2-ITS 230V 50Hz		

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 250 K302-A2-ITS 230V 50Hz	160 mm	139 mm	76 mm	65 mm	6.2 mm

