



# HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

## BSN 100/70 K302-A2-TS 230V 50Hz

Impregnated electromagnetic copper/iron double-wattage ballasts for use with an external series (superimposed) ignitor for CDO, MH, HPI (Plus) and SON lamps

### Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BSN 100/70 K302-A2-TS 230V 50Hz

Full product name	BSN 100/70 K302-A2-TS 230V 50Hz
Full product code	871869674112200
Order code	74112200
Material Nr. (12NC)	913700753326
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696741122
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696741139

HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 100/70 K302-A2-TS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm

