



# Core & Coil (71A) MH 175W - 450W

## CORE & COIL HID MH BAL 175W M137/M152 480V/120T C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information	
ANSI Code	M137-M152
Lamp Type	175W MH
Number of Lamps	1 piece/unit
Circuit Type	SUPER-CWA
Ballast Type	Magnetic HID
Base Model	71A5541TEE
Core Size	4 1/4 x 4 3/4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI533-H4
Ignitor Temperature Rating	105°C
Capacitor Value	11 MFD
Capacitor Catalog Number	7C110M40
Capacitor Requirements	370V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.65 in
Capacitor Height	3.75 in
Automatic Restart	No

Operating and Electrical	
Input Voltage	480/120T V
Input Frequency	60 Hz
Input Current (Open Circuit)	0.31 A
Input Current (Starting)	0.17 A
Input Current (Short Circuit)	0.13-0.2 A
Secondary Short Circuit Current	1.67-2 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	285 V
Input Current (Nom)	0.42 A A
Input Power (Nom)	198 W
Rated Lamp Power	175 W

Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes


## Core & Coil (71A) MH 175W - 450W

Max Ballast-Lamp Distance Remote Wiring 2'	
Recommended Fuse Value	2 A
<b>Approval and Application</b>	
Open Circuit Voltage Test (Volts)	260-305 V
Approval Marks	ULR CSA certificate EISA RoHS Compliant
Temperature Marking	A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029A

### Product Data

Order product name	CORE & COIL HID MH BAL 175W M137/M152 480V/120T C&C
EAN/UPC - Product	781087080924
Order code	913701102102
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	913701102102
Net Weight (Piece)	4.523 kg

### Dimensional drawing



MH BAL 175 M137/152 480V/120T C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5541500DTEE	3.7 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in

