



# Core & Coil (71A) MH ~LT~ 175W

## CORE & COIL HID MH BAL 35/39W M130 120/277V C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

#### **Product data**

General Information					
ANSI Code	M130				
Lamp Type	35/39W MH				
Number of Lamps	1 piece/unit				
Circuit Type	HX-HPF				
Ballast Type	Magnetic HID				
Base Model	71A5081				
Core Size	3 X 4 (2 coil)				
Suitable For Outdoor Use	Yes				
Ignitor Catalog Number	LI533-H4				
Ignitor Temperature Rating	105°C				
Capacitor Value	5 MFD				
Capacitor Catalog Number	7C050L30RA				
Capacitor Requirements	277V				
Capacitor Temperature Rating	105°C				
Capacitor Diameter/Oval Dimensions	1.25 in				
Capacitor Height	2.25 in				
Automatic Restart	No				

Operating and Electrical					
Input Voltage	120/277 V				
Input Frequency	60 Hz				
Input Current (Open Circuit)	0.9/0.4 A				
Input Current (Starting)	0.5/0.22 A				
Input Current (Short Circuit)	0.35-0.55/0.15-0.25 A				
Secondary Short Circuit Current	0.6-0.75/0.6-0.75 A				
Constant Wattage Deviation	10%				
Ballast Factor (Nom)	1				
Power Factor (Nom)	0.90				
Open Circuit Voltage	230 V				
Input Current (Nom)	0.45/0.2 A A				
Input Power (Nom)	56 W				
Rated Lamp Power	35/39 W				
Wiring					
Wire Striplength	0.5 mm				
Wire Length by Color	12"				
Wire Type	Stranded				
Remote Wiring Configuration Allowed	Yes				


Datasheet, 2019, February 12 data subject to change

### Core & Coil (71A) MH ~LT~ 175W

Max Ballast-Lamp Distance Remote Wiring 15'				
Recommended Fuse Value	3/1 A			
Approval and Application				
Open Circuit Voltage Test (Volts)	205-255 V			
Approval Marks	ULR CSA certificate RoHS Compliant			
Temperature Marking	B/A			
UL Recognized	Yes			
Hipot Test (1 Minute)	2000 V			
Hipot Test (2 Seconds)	2500 V			
UL Insulation Class	H(180°C)			
UL Temperature Code	1029B			

Product Data				
Order product name	CORE & COIL HID MH BAL 35/39W M130			
	120/277V C&C			
EAN/UPC - Product	781087069028			
Order code	913701136802			
Numerator - Quantity Per Pack	1			
Numerator - Packs per outer box	6			
Material Nr. (12NC)	913701136802			
Net Weight (Piece)	0.001 kg			

#### Dimensional drawing



MH BAL 35/39W M130 120/277V C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5081500D	2.1 in	0.8 in	3.9 in	3.5 in	2.8 in	2.4 in

