



Core & Coil (71A) HPS 200W - 400W

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information			
ANSI Code	S50	Input current (short circuit)	1.24-1.87/0.71-1.06 A
Lamp type	250W HPS	Secondary short-circuit current	3.7-4.5 A
Number of lamps	1 piece/unit	Constant wattage deviation	Within Trapezoid
Circuit type	CWA	Ballast factor (nom.)	1
Ballast type	Magnetic HID	Power factor (nom.)	0.90
Base model	71A82H1A	Open circuit voltage	189 V
Core size	4 x 4 (2 coil)	Input current (nom.)	2.50/1.40 A A
Suitable for outdoor use	Yes	Input power (nom.)	295 W
Ignitor catalogue number	LI501-H4	Rated lamp power	250 W
Ignitor temperature rating	105°C		
Capacitor value	35 MFD	Wiring	
Capacitor catalogue number	7C350P24RA	Wire strip length	0.5 mm
Capacitor requirements	240V	Wire length by colour	12"
Capacitor temperature rating	105°C	Wire type	Stranded
Capacitor diameter/oval dimensions	1.65 in	Remote wiring configuration allowed	Yes
Capacitor height	3.7 in	Max. ballast-lamp distance remote wiring	5'
Automatic restart	No	Recommended fuse value	7/4 A
Operating and Electrical			
Input voltage	127/220 V	Approval and Application	
Input frequency	60 Hz	Open circuit voltage test (volts)	175-205 V
Input current (open circuit)	1.25/0.75 A	Approval marks	ULR NOM certificate RoHS Compliant
Input current (starting)	1.80/1.04 A	Temperature marking	A/A
		UL recognised	Yes
		Hipot test (1 minute)	2000 V

Core & Coil (71A) HPS 200W – 400W


Hipot test (2 seconds)	2500 V
UL insulation class	H(180°C)
UL temperature code	1029A

Product Data

Order product name	CORE & COIL HID HPS BAL 250W S50 127/220V C&C
--------------------	--

EAN/UPC – product	781087096802
Numerator – quantity per pack	1
Numerator – packs per outer box	2
Material no. (12NC)	913701146012
Net weight (piece)	5.385 kg

Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 250W S50 127/220V C&C	3.55 in	1.82 in	4.8 in	4.4 in	4.3 in	3.9 in

HPS BAL 250W S50 127/220V C&C

