

## Core & Coil (71A) HPS ~LT~ 200W

**CORE & COIL HID HPS BAL 150W (EURO LAMP)  
220/240V C&C**

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

## Product data

General Information	
ANSI Code	SON-TPIA
Lamp Type	150W HPS
Number of Lamps	1 piece/unit
Circuit Type	LEAD-REACTOR
Ballast Type	Magnetic HID
Base Model	71A9918
Core Size	2 5/8 x 2 3/16
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI533-H4
Ignitor Temperature Rating	105°C
Capacitor Value	17 MFD
Capacitor Catalog Number	7C170P40
Capacitor Requirements	300V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.75 in
Capacitor Height	3.75 in
Automatic Restart	No

## Operating and Electrical

<b>Input Voltage</b>	220/240 V
<b>Input Frequency</b>	60 Hz
<b>Input Current (Open Circuit)</b>	1.41/1.53 A
<b>Input Current (Starting)</b>	0.88/0.71 A
<b>Input Current (Short Circuit)</b>	0.68-1.02/0.57-0.85 A
<b>Secondary Short Circuit Current</b>	1.77-2.67 A
<b>Constant Wattage Deviation</b>	10%
<b>Ballast Factor (Nom)</b>	1
<b>Power Factor (Nom)</b>	0.90
<b>Open Circuit Voltage</b>	220 V
<b>Input Current (Nom)</b>	0.78/0.72 A A
<b>Input Power (Nom)</b>	167 W
<b>Rated Lamp Power</b>	150 W

## Wiring


Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes

Core & Coil (71A) HPS ~LT~ 200W

Max Ballast-Lamp Distance Remote Wiring 2'	
Recommended Fuse Value	4/4 A
Approval and Application	
Open Circuit Voltage Test (Volts)	202-233 V
Approval Marks	NOM certificate RoHS Compliant
Temperature Marking	A/A
UL Recognized	No
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029A

Product Data	
Order product name	CORE & COIL HID HPS BAL 150W (EURO LAMP) 220/240V C&C
EAN/UPC - Product	781087109007
Order code	913701147602
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	913701147602
Net Weight (Piece)	1.756 kg

Dimensional drawing



HPS BAL 150W (EURO LAMP) 220/240V C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 150W (EURO LAMP) 220/240V C&C	4.1 in	2.74 in	2.6 in	2.2 in	2.2 in	1.8 in

