



Centium T8 Instant Start

CENTIUM ELE BALLAST (4) F32T8 120-277V

Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology.

Product data


General information		Wiring	
Lamp Type	F32T8	Color Input Terminals	No terminals
Number of Lamps	3/4 piece/unit	Color Output Terminals	No terminals
Ballast Type	Electronic Fluorescent	Wire Striplength	0.50/0.375 mm
Base Model	ICN4P32N	Lamp Connection	Parallel
Suitable For Outdoor Use	Yes	Wire Length by Color	See data sheet
Automatic Restart	Yes	Wire Gauge (Nom)	18AWG mm
Operating and electrical		Wire Type	Solid
Input Voltage	120 to 277 V	Remote Wiring Configuration Allowed	Yes
Input Frequency	50 to 60 Hz	Tandem Wiring Configuration Allowed	Yes
Total Harmonic Distortion USA	10 %	Through Wiring Configuration Allowed	Yes
Ignition Method	Instant Start	Max Ballast-Lamp Distance Remote Wiring	ES = 6' / Standard = 20'
Crestfactor (Nom)	1.7	Max Ballast-Lamp Distance Tandem Wiring	ES = 6' / Standard = 20'
Ignition Time (Nom)	0.1 s	Max Ballast-Lamp Distance Through Wiring	ES = 6' / Standard = 20'
Ballast Factor (Nom)	0.89	Connector Type	No connector
Power Factor (Nom)	0.98	Temperature	
Input Current (Max)	0.94 A	T-Case Maximum (Nom)	70 °C
Input Current (Min)	0.41 A	Mechanical and housing	
Input Power (Nom)	111 W	Housing Material	Metal
Rated Lamp Power	32 W	Housing	N

Centium T8 Instant Start

Housing Dimensions	9.5" x 1.3" x 1.0"
Approval and application	
EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate CEC Listing CEE Rated NEMA Premium NOM certificate RoHS Compliant
Hum And Noise Level	A
UL Recognized	No
Product data	
Order product name	CENTIUM ELE BALLAST (4) F32T8 120-277V

EAN/UPC - Product	781087091517
Order code	913701220302
Numerator - Quantity Per Pack	1
Local code description	ICN4P32N35M
Numerator - Packs per outer box	30
Material Nr. (12NC)	913701220302
Net Weight (Piece)	0.441 kg

Dimensional drawing



CENTIUM ELE BALLAST (4) F32T8 120-277V

Product
CENTIUM ELE BALLAST (4) F32T8 120-277V

