

ROVR

ROVR INTLV DIM (1) F28T5_NO SALE TO CALIF

Philips Advance ROVR ballasts reflect the latest approach to controlling fluorescent lighting. Rather than simply responding to instructions from control components, ROVR ballasts enable twoway communication, and have the ability to dim and switch individual ballasts through the control signal. These features allow for virtually unlimited design flexibility while creating sustainable lighting systems. This two-way communication is made possible through the industry-standard digital communication protocol known as DALI (Digital Addressable Lighting Interface). This protocol allows ROVR ballasts to provide users with operational data while controlling the output of individual luminaires. This fully supports sustainable design principles such as daylight harvesting and occupancy sensors while enabling a proactive response to maintenance concerns.

Product data

General Information	
Lamp Type	F28T5
Number of Lamps	1 piece/unit
Ballast Type	Dimmable Fluorescent
Base Model	IDA128D
Suitable For Outdoor Use	Yes
Automatic Restart	Yes

Operating and Electrical	
Input Voltage	120 to 277 V
Input Frequency	50 to 60 Hz
Max THD	10 %
Starting Method	Programmed Start
Lamp Current Crest Factor (Nom)	1.7
Ignition Time (Nom)	1.5 s
Ballast Factor (Max)	1

Ballast Factor (Min)	0.03
Power Factor (Nom)	0.98
Input Current (Operating) (Max)	0.27 A
Input Current (Operating) (Min)	0.12 A
Input Power (Max)	32 W
Input Power (Min)	7 W
Rated Lamp Watts	28 W


Wiring	
Color Input Terminals	BLK, WHT & PUR
Color Output Terminals	RED & BLU
Wire Striplength	0.375 mm
Control Wire Gauge	18AWG
Lamp Connection	Series
Wire Length by Color	No wires
Wire Gauge (Nom)	18AWG mm

ROVR

Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	No
Through Wiring Configuration Allowed	No
Max Ballast-Lamp Distance Remote Wiring	6'
Max Ballast-Lamp Distance Tandem Wiring	NA
Max Ballast-Lamp Distance Through Wiring	NA
Connector Type	Poke-In
Temperature	
T-Case Maximum (Nom)	70 °C
Mechanical and Housing	
Housing Material	Metal
Housing	D
Housing Dimensions	16.7" x 1.18" x 1.0"
Approval and Application	
EMC Immunity Standard	FCC Consumer

Approbation Marks	CSA certificate UL certificate CEC Listing RoHS Compliant
Sound Rating	A
UL Recognized	No
Product Data	
Order product name	ROVR INTLV DIM (1) F28T5_NO SALE TO CALIF
EAN/UPC - Product	781087095072
Order code	IDA128D35M
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913701223102
Net Weight (Piece)	0.441 kg

Dimensional drawing



ELE DIMMING BALLAST (1) F28T5 120-277V

Product	A1	A2	B1	C1
ROVR IDA128D35M	16.70 in	16.34 in	1.18 in	1.00 in

