

# Optanium T8 Programmed Start

## OPTANIUM ELE BALLAST (2) F32T8 347-480V

Philips Advance Optanium high-efficiency electronic ballasts are engineered to optimize lighting performance and maximize energy savings. These ballasts provide an unparalleled package of features and benefits to support the wide variety of T8 fluorescent lamps out in the market place.

### Product data

General Information	
Lamp Type	F32T8
Number of Lamps	1/2 piece/unit
Ballast Type	Electronic Fluorescent
Base Model	HOP2PSP32HLL
Suitable For Outdoor Use	Yes
Automatic Restart	Yes
Operating and Electrical	
Input Voltage	347-480 V
Input Frequency	50 to 60 Hz
Max THD	10 %
Starting Method	Programmed Start
Lamp Current Crest Factor (Nom)	1.6
Ignition Time (Nom)	1.5 s
Ballast Factor (Nom)	1.2
Power Factor (Nom)	0.98
Input Current (Operating) (Max)	0.23 A
Input Current (Operating) (Min)	0.17 A
Input Power (Nom)	79-79 W


Rated Lamp Watts	32 W
Wiring	
Color Input Terminals	No terminals
Color Output Terminals	No terminals
Wire Striplength	0.50/0.375 mm
Lamp Connection	Parallel
Wire Length by Color	See data sheet
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	Yes
Through Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	20'
Max Ballast-Lamp Distance Tandem Wiring	Any = 20'
Max Ballast-Lamp Distance Through Wiring	Any = 20'
Connector Type	No connector

## Optanium T8 Programmed Start

<b>Temperature</b>	
T-Case Maximum (Nom)	90 °C
<b>Mechanical and Housing</b>	
Housing Material	Metal
Housing	L
Housing Dimensions	16.7" x 1.18" x 1.0"
<b>Approval and Application</b>	
EMC Immunity Standard	FCC Non-Consumer
Approbation Marks	CSA certificate UL certificate CEC Listing CEE Rated CSA E RoHS Compliant
Sound Rating	A

UL Recognized	No
<b>Product Data</b>	
Order product name	OPTANIUM ELE BALLAST (2) F32T8 347-480V
EAN/UPC - Product	781087131336
Order code	HOP2PSP32HLL35M
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	913701252502
Net Weight (Piece)	531.000 g

### Dimensional drawing



ELE BALLAST (2) F32T8 347-480V

Product	A1	A2	B1	C1
OPTANIUM ELE BALLAST (2) F32T8 347-480V	16.70 in	16.34 in	1.18 in	1.00 in

