



Optanium T8 Programmed Start

OPTANIUM ELE BALLAST (2) F32T8 120-277V

Philips Advance Optanium high-efficiency electronic ballasts are engineered to optimize lighting performance and maximize energy savings. These ballasts provide an unparalleled package of features and benefits to support the wide variety of T8 fluorescent lamps out in the market place.

产品数据

基本信息	
灯具类型	F32T8
灯具数量	1/2 件/单位
镇流器类型	Electronic Fluorescent
基本型号	IOP2PSP32N
适用于户外	Yes
自动重新启动	Yes
运营和电气	
输入电压	120-277 V
输入频率	50 至 60 岁 Hz
美国总谐波变形	10 %
点火方法	程式化启动
峰值因数 (标称)	1.6
点火时间 (标称)	1.5 s
镇流器因数 (标称)	0.89
功率系数 (标称)	0.98
输入电流 (最大)	0.20 A
输入电流 (最小)	0.47 A
输入功率 (标称)	56-55 W


额定照明功率	32 W
接线方式	
颜色输入端	No terminals
颜色输出端	No terminals
电线裸线长度	0.50/0.375 mm
灯具连接	Parallel
按颜色区分的电线长度	See data sheet
电线规格 (标称)	18AWG mm
电线类型	Solid
允许的远程布线配置	Yes
允许的串联布线配置	Yes
允许的通过式布线配置	Yes
最大镇流器到灯具距离远程布线	ES = 6' / Standard = 20'
最大镇流器到灯具距离串联布线	ES = 6' / Standard = 20'
最大镇流器到灯具距离通过式布线	ES = 6' / Standard = 20'
连接器类型	No connector

Optanium T8 Programmed Start

温度	
最大外壳温度 (标称)	70 °C
机械和壳体	
外壳材料	金属
外壳	N
外壳尺寸	9.5" x 1.3" x 1.0"
应用	
Emc 抗干扰标准	FCC Non-Consumer
批准标志	CSA 认证证书 UL 认证证书 CEC Listing CEE Rated NEMA Premium RoHS Compliant
温度和噪声级别	A

UL 认证	No
产品参数	
订单产品名称	OPTANIUM ELE BALLAST (2) F32T8 120-277V
EAN/UPC - 产品	781087134733
订购代码	913701260602
计算器 - 每个包中的数量	1
计算器 - 每个外包装箱中的包数	30
材料编号(12NC)	913701260602
净重 (每件)	350.000 g

二维绘图



Product	A1	A2	B1	C1
OPTANIUM ELE BALLAST (2) F32T8 120-277V	9.50 in	8.90 in	1.30 in	1.00 in

